


- ★1. Remove the plug when using the port (6 Hex. Soc.). Also the pilot port adapter is not standard accessory, so it must be ordered separately referring to the "Pilot Port" on page 179.
- *2. Install the pump so that the "Filling Port" is at the top.

 *3. Do not touch the screw because it is adjusted at the time of shipment.

Model Numbers	A	В	С	D	Е	F	Н	J	K	L	N	P	Q	R	S	Т	U	Mounting Flange	Connecting Port	Pipe Flange Threads
A3HG71-FR09V*-K-E1D/E2D	M12	22	M27×2	60	9	32 +0.018 +0.002	35 +0.018 -0.288	160 0 -0.063	50	M10	22	10-0.036	190	141.4	18	35	192	Conforms to ISO 3019-2	Metric	Metric
A3HG71-FR09V*-K-U1D	1/2-13 UNC	21	G 3/4	56	12.7	31.75 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	35.32 0 -0.18	127 -0.05	48		19	$7.94^{+0.03}_{0}$	143	114.5	13.5	28	155	Conforms to ISO 3019-1	Unified	Unified
A3HG71-FR09V*-K-U2D	M12	22	G 3/4	56	12.7	31.75 -0.05	35.32 -0.18	127 -0.05	48	5/16-18 UNC	19	7.94 +0.03	143	114.5	13.5	28	155	Conforms to ISO 3019-1	BSPP	Metric
A3HG71-FR09V*-K-J1D	M12	22	G 3/4	56	12.7	31.75 0 -0.05	35.32 0 -0.18	127 -0.05	48	0110	19	7.94 +0.03	143	114.5	13.5	28	155	Conforms to ISO 3019-1	Rc	Metric

Flange Mtg.: A3HG100-FR09V*-K-E1D/E2D/U1D/U2D/J1D

View Arrow X



accessory, so it must be ordered separately referring to the "Pilot Port" on page 179. ★2. Install the pump so that the "Filling Port" is at the top.

★3. Do not touch the screw because it is adjusted at the time of shipment.

Model Numbers	A	В	С	D	Е	F	Н	J	K	L	N	P	Q	R	S	Т	Mounting Flange	Connecting Port	Pipe Flange Threads
A3HG100-FR09V*-K-E1D/E2D	M12	22	M27×2	80	9	56	40 +0.018 +0.002	43 +0.018 -0.288	180 0 -0.063	70	M12	28	12 -0.043	158.4	18	35	Conforms to ISO 3019-2	Metric	Metric
A3HG100-FR09V*-K-U1D	1/2-13 UNC	21	G 3/4	62	12.7	45	38.1 0	42.36 -0.18	152.4 0.05	54		28	9.53 +0.03	161.6	21.5	39	Conforms to ISO 3019-1	Unified	Unified
A3HG100-FR09V*-K-U2D	M12	22	G 3/4	62	12.7	45	38.1 0	42.36 -0.18	152.4 0 -0.05	54	7/16-14 UNC	28	9.53 +0.03	161.6	21.5	39	Conforms to ISO 3019-1	BSPP	Metric
A3HG100-FR09V*-K-J1D	M12	22	G 3/4	62	12.7	45	38.1 -0.05	42.36 0	152.4 0	54	0110	28	9.53+0.03	161.6	21.5	39	Conforms to ISO 3019-1	Rc	Metric

Pilot Port

F

View Arrow X

Pilot Port is common to that of "A3HG16-FR07K-E1C/U1C/U2C/J1C" (except the height dimension from the center of the pump). Refer to page 179 for the dimensions of Pilot Port.

Drain Port is common to that of pressure compensator model.Refer to page 172 or 173 for the dimensions of Drain Port.

Foot Mtg.:A3HG71-LR09V*-K-E1D/E2D/U1D/U2D/J1D, A3HG100-LR09V*-K-E1D/E2D/U1D/U2D/J1D Mounting bracket is common to that of pressure compensator model (except max height dimension). Refer to page 172 and 173 for the dimensions of mounting bracket.